



**Studbolt with 2 heavy  
hexagon nuts ASME B16.5/  
B18.2.2 Steel ASTM A193  
- ASTM A194 Plain Gr.B7 -  
Gr.2H 7/8X420 (16.1/2)**

|                |               |
|----------------|---------------|
| Article number | 22080.222.419 |
| Brand          | -             |
| UBB            | 500578027178  |
| UNSPSC         | 31161619      |
| EAN            | 8715494343725 |
| PKG. of 1      | Full Box Only |

**Technical Parameters**

|                    |                         |
|--------------------|-------------------------|
| Diameter           | 7/8 Inch                |
| Length             | 420 mm                  |
| Class              | Gr.B7 - Gr.2H           |
| Material           | Steel                   |
| Material technical | ASTM A193 - ASTM A194   |
| Thread direction   | Right                   |
| Surface treatment  | Plain                   |
| Thread             | Unified National Coarse |
| Threads per inch   | 9                       |

|      |                                                                                                                                                                                                                     |
|------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Info | Tolerances of the total length of the studbolts according to ASME B16.5<br>Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends. |
|------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

**Standards**

|      |               |
|------|---------------|
| BS   | ≈4882         |
| ASTM | A193/A194     |
| ASME | B16.5/B18.2.2 |

**Technical Specification**

|   |        |
|---|--------|
| B | 1.4375 |
|---|--------|

**Technical Drawing**

L (mm) 420

M 21.8

