



Machine screw pan head UNC asme B18.6.3 ASME B18.6.3 Steel Zinc plated #6-32X3/8

Article number	24668.035.009
Brand	-
UBB	500668229957
UNSPSC	31161504
EAN	8712423049406
PKG. of 1	Full Box Only

Technical Parameters

Diameter	NO.6
Length	3/8 Inch
Driving features	Pozidriv
Head shape	Pan head
Material	Low carbon steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Unified National Coarse
Threads per inch	32

Info

Screws with diameter \leq No.5 and length \leq 1.1/8 inch are fully threaded, longer screws are threaded 1 inch min. Screws with diameter No.5 and length \leq 2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.

Standards

ASME	B18.6.3
------	---------

Technical Specification

A (max.)	0.27
H (max.)	0.097

Technical Drawing

FABORY

