



**Machine screw round hd slt/
ph comb UNC asme B18.6.3
ASME B18.6.3 Low carbon
steel Zinc plated #8-32X2
Inch**

Article number	U24212.016.0200
Brand	-
UBB	500624923974
UNSPSC	31161504
EAN	8717077799714
PKG. of 1	Full Box Only

Technical Parameters

Diameter	NO.8
Length	2 Inch
Driving features	Slotted/Phillips Combination
Head shape	Round head
Material	Low carbon steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Unified National Coarse
Threads per inch	32

Info	Screws with diameter \leq No.5 and length \leq 1.1/8 inch are fully threaded, longer screws are threaded 1 inch min.Screws with diameter No.5 and length \leq 2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.
------	---

Standards

ASME	B18.6.3
------	---------

A (max.)	0.309
H (max.)	0.12
J (max.)	0.054
No. cross recess	2
T (max.)	0.077

